FGS-MEXP-A/B/F



FiberGuide® 2-Inch Express Exit™, 4x4, 4x6, 4x12in, Yellow

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Express exit
Product Brand FiberGuide®

Product Series FGS

General Specifications

Color Yellow
Orientation Horizontal

Section Type Express exit

Dimensions

 Height
 125 mm | 4.921 in

 Width
 254 mm | 10 in


System Dimensions 102 mm x 102 mm (4 in x 4 in) | 102 mm x 152 mm (4 in x 6 in) | 102 mm x 305 mm (4 in x 12

in) | 102 mm x 610 mm (4 in x 24 in)


Ordering Tree



FGS-MEXP-A/B/F



Section Color



Section Size

A/B/F	4 x 4/6/12 in, with 2 x 2 in exit
20	4 x 4/6/12 III, WILII 2 x 2 III exit
E-A/B/F	4 x 4/6/12 in, with 4 x 4 in exit
F-F/H-NC	4 x 12/18/24 in, with 4 x 12 in exit, no cover
G-A/B/F	4 x 4/6/12 in, with 4 x 6 in exit
LP-A/B/F	4 x 4/6/12 in, with 2 x 2 in exit, low profile
LP-CA	4 x 4/6/12 in, with 2 x 4 in exit, low profile
LP-G	2 x 6 in, with 2 x 2 in exit, low profile
GS-ABF-NC	4 x 4/6/12 in, with 4 x 6 in exit, no cover
CV	cover
NC	no cover
	F-F/H-NC G-A/B/F LP-A/B/F LP-CA LP-G GS-ABF-NC CV

Material Specifications

Material Type Engineering Thermoplastic

Environmental Specifications

Flammability Rating CSA S143 | UL 2024 | UL 94 V-0

Halogen Characteristics Blue Angel | TCO '99 | WEEE

Safety Standard CSA | UL

Packaging and Weights

Weight, net 0.98 kg | 2.161 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

