



FIST GPST Fiber Patch/Splice Tray, 12/24 ports, no adapters, SMOUV splice chip, 19 in, gray, right patch cord routing

Product Classification

| | |
|------------------------------|-------------------------|
| Brand | FIST™ |
| Product Series | FIST-GPST |
| Product Type | Fiber patch/splice tray |
| Regional Availability | EMEA |

Construction Materials

| | |
|-------------------|------------|
| Fiber Mode | Singlemode |
|-------------------|------------|

Dimensions

| | |
|---------------|----------------------|
| Depth | 190.00 mm 7.48 in |
| Height | 18.00 mm 0.71 in |
| Width | 355.00 mm 13.98 in |

Environmental Specifications

| | |
|------------------------------|--------------------------------------|
| Operating Temperature | -5 °C to +45 °C (+23 °F to +113 °F) |
| Relative Humidity | Up to 93%, non-condensing |
| Storage Temperature | -30 °C to +60 °C (-22 °F to +140 °F) |

General Specifications

| | |
|------------------------------|----------------------------------|
| Color | Gray |
| Functionality | Patching Splicing |
| Package Quantity | 1 |
| Splicing Type | Heat shrink, single fiber fusion |
| Total Ports, quantity | 12 |

Mechanical Specifications

| | |
|----------------------------------|-------------------|
| Patch Cord Entry Location | Front, right side |
|----------------------------------|-------------------|

Regulatory Compliance/Certifications

Agency

Classification

RoHS 2011/65/EU

Compliant

