



FIST GPST Fiber Patch/Splice Tray, 24 ports, LC/APC, singlemode, SMOUV splice chip, 19 in, gray, right patch cord routing

Product Classification

Brand	FIST™
Product Series	FIST-GPST
Product Type	Fiber patch/splice tray
Regional Availability	EMEA

Construction Materials

Fiber Mode	Singlemode
-------------------	------------

Dimensions

Depth	190.00 mm 7.48 in
Height	18.00 mm 0.71 in
Width	355.00 mm 13.98 in

Environmental Specifications

Operating Temperature	-5 °C to +45 °C (+23 °F to +113 °F)
Relative Humidity	Up to 93%, non-condensing
Storage Temperature	-30 °C to +60 °C (-22 °F to +140 °F)

General Specifications

Color	Gray
Functionality	Patching Splicing
Interface Feature, front	APC
Interface, front	LC
Package Quantity	1
Splicing Type	Heat shrink, single fiber fusion
Total Ports, quantity	24

Mechanical Specifications

Patch Cord Entry Location	Front, right side
----------------------------------	-------------------

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant

