



FIST GPST Fiber Patch/Splice Tray, 12 ports, SC/APC, singlemode, preterminated with pigtails, SMOUV splice chip, 19 in, gray, left patch cord routing

## Product Classification

<b>Brand</b>	FIST™
<b>Product Series</b>	FIST-GPST
<b>Product Type</b>	Fiber patch/splice tray
<b>Regional Availability</b>	EMEA

## Construction Materials

<b>Fiber Mode</b>	Singlemode
-------------------	------------

## Dimensions

<b>Depth</b>	190.00 mm   7.48 in
<b>Height</b>	18.00 mm   0.71 in
<b>Width</b>	355.00 mm   13.98 in

## Environmental Specifications

<b>Operating Temperature</b>	-5 °C to +45 °C (+23 °F to +113 °F)
<b>Relative Humidity</b>	Up to 93%, non-condensing
<b>Storage Temperature</b>	-30 °C to +60 °C (-22 °F to +140 °F)

## General Specifications

<b>Color</b>	Gray
<b>Functionality</b>	Patching   Splicing
<b>Interface Feature, front</b>	APC
<b>Interface, front</b>	SC
<b>Package Quantity</b>	1
<b>Splicing Type</b>	Heat shrink, single fiber fusion
<b>Total Ports, quantity</b>	12

## Mechanical Specifications

<b>Patch Cord Entry Location</b>	Front, left side
----------------------------------	------------------

## Regulatory Compliance/Certifications

**Agency**

RoHS 2011/65/EU

**Classification**

Compliant

