

FIST-SODF2-Fiber Termination/Splice Block, pre-terminated with pigtailed, 24 SC/APC, singlemode, gray

Product Classification

Brand	FIST™
Product Series	FIST-SODF2
Product Type	Fiber patch/splice block
Regional Availability	EMEA

Construction Materials

Fiber Mode	Singlemode
-------------------	------------

Environmental Specifications

Operating Temperature	-5 °C to +45 °C (+23 °F to +113 °F)
Relative Humidity	Up to 93%, non-condensing
Storage Temperature	-30 °C to +60 °C (-22 °F to +140 °F)

General Specifications

Application	Used in FIST-SODF-style frames only
Color	Gray
Color, front	Gray
Functionality	Patching Splicing
Includes	Mounting hardware
Interface Feature, front	APC
Interface, front	SC
Package Quantity	1
Total Ports, quantity	24

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

