

OMX Fiber Termination Block with IFC cable, 144 LC/UPC, singlemode, putty white, left, 100 meters, Stub tail at far end

Product Classification

Brand	OMX600®
Product Series	OMX
Product Type	Fiber patch block, with IFC cable
Regional Availability	EMEA Latin America North America

Construction Materials

Fiber Mode	Singlemode
Finish	Powder coated
Material Type	Steel

Dimensions

Cable Stub Length	100 m 328 ft
Depth	283.21 mm 11.15 in
Height	373.00 mm 14.69 in
Width	203.20 mm 8.00 in

General Specifications

Shelf Movement	Hinged
Application	Used in OMX-style frames only
Body Style	Left orientation
Cable Stub Type	IFC
Color	Putty white
Color, front	Putty white
Functionality	Patching
Growth Configuration	Fully loaded
Interface Feature, front	Standard
Interface, front	LC
Interface, rear	Stub tail
Package Quantity	1
Rack Type	OMX
Total Ports, quantity	144

Mechanical Specifications

Cable Exit Location	Upward
----------------------------	--------

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant

