



OMX Fiber Termination Block, pre-terminated with pigtails, 96 SC/UPC, singlemode, putty white, right oriented

## Product Classification

<b>Brand</b>	OMX600®
<b>Product Series</b>	OMX
<b>Product Type</b>	Fiber patch block
<b>Regional Availability</b>	EMEA   Latin America   North America

## Construction Materials

<b>Fiber Mode</b>	Singlemode
<b>Finish</b>	Powder coated
<b>Material Type</b>	Steel

## Dimensions

<b>Depth</b>	283.21 mm   11.15 in
<b>Height</b>	373.00 mm   14.69 in
<b>Width</b>	203.20 mm   8.00 in

## General Specifications

<b>Shelf Movement</b>	Hinged
<b>Application</b>	Used in OMX-style frames only
<b>Body Style</b>	Right orientation
<b>Color</b>	Putty white
<b>Color, front</b>	Putty white
<b>Functionality</b>	Patching
<b>Growth Configuration</b>	Fully loaded
<b>Interface Feature, front</b>	Standard
<b>Interface, front</b>	SC
<b>Package Quantity</b>	1
<b>Rack Type</b>	OMX
<b>Total Ports, quantity</b>	96

## Regulatory Compliance/Certifications

**Agency**

RoHS 2011/65/EU

**Classification**

Compliant

