



OMX Fiber Termination Block, pre-terminated with pigtails, 96 SC/UPC, multimode, putty white, left oriented

Product Classification

Brand	OMX600®
Product Series	OMX
Product Type	Fiber patch block
Regional Availability	EMEA Latin America North America

Construction Materials

Fiber Mode	Multimode
Finish	Powder coated
Material Type	Aluminum

Dimensions

Depth	283.21 mm 11.15 in
Height	373.00 mm 14.69 in
Width	203.20 mm 8.00 in

General Specifications

Shelf Movement	Hinged
Application	Used in OMX-style frames only
Body Style	Left orientation
Color	Putty white
Color, front	Putty white
Functionality	Patching
Growth Configuration	Fully loaded
Interface Feature, front	Standard
Interface, front	SC
Package Quantity	1
Rack Type	OMX
Total Ports, quantity	96

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant

