



Next Generation Frame (NGF) Fiber Termination Block with IFC Cable, singlemode, 192 LC/UPC to Stub tail, left oriented, upward cable exit, black, 40 m

## Product Classification

<b>Product Series</b>	NGFB
<b>Product Type</b>	Fiber patch block, with IFC cable
<b>Regional Availability</b>	EMEA   Latin America   North America

## Construction Materials

<b>Fiber Mode</b>	Singlemode
<b>Finish</b>	Powder coated
<b>Material Type</b>	Steel

## Dimensions

<b>Cable Stub Length</b>	40 m   131 ft
--------------------------	---------------

## Environmental Specifications

<b>Operating Temperature</b>	-5 °C to +50 °C (+23 °F to +122 °F)
<b>Qualification Standards</b>	Telcordia GR-449-CORE
<b>Relative Humidity</b>	Up to 80%, non-condensing
<b>Storage Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)

## General Specifications

<b>Shelf Movement</b>	Fixed
<b>Application</b>	Used in NGF-style frames only
<b>Body Style</b>	Left orientation
<b>Cable Stub Type</b>	IFC, ribbon
<b>Color</b>	Black
<b>Color, front</b>	Black
<b>Door Type, front</b>	Compression latch   Hinged
<b>Functionality</b>	Patching
<b>Growth Configuration</b>	Fully loaded
<b>Interface Feature, front</b>	Standard
<b>Interface, front</b>	LC
<b>Interface, rear</b>	Stub tail

**Package Quantity** 1  
**Rack Type** NGF  
**Total Ports, quantity** 192

## Mechanical Specifications

**Cable Exit Location** Upward

## Regulatory Compliance/Certifications

**Agency**  
RoHS 2011/65/EU

**Classification**  
Compliant

