



Next Generation Frame (NGF) Fiber Termination Block with IFC Cable, singlemode, 192 LC/UPC to Stub tail, right oriented, upward cable exit, black, 40 m

Product Classification

Product Series	NGFB
Product Type	Fiber patch block, with IFC cable
Regional Availability	EMEA Latin America North America

Construction Materials

Fiber Mode	Singlemode
Finish	Powder coated
Material Type	Steel

Dimensions

Cable Stub Length	40 m 131 ft
--------------------------	---------------

Environmental Specifications

Operating Temperature	-5 °C to +50 °C (+23 °F to +122 °F)
Qualification Standards	Telcordia GR-449-CORE
Relative Humidity	Up to 80%, non-condensing
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

Shelf Movement	Fixed
Application	Used in NGF-style frames only
Body Style	Right orientation
Cable Stub Type	IFC, ribbon
Color	Black
Color, front	Black
Door Type, front	Compression latch Hinged
Functionality	Patching
Growth Configuration	Fully loaded
Interface Feature, front	Standard
Interface, front	LC
Interface, rear	Stub tail

Package Quantity 1
Rack Type NGF
Total Ports, quantity 192

Mechanical Specifications

Cable Exit Location Upward

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

