



Next Generation Frame (NGF) Fiber Termination Block with IFC Cable, singlemode, 96 SC/APC to Stub tail, left oriented, upward cable exit, putty white, 20 m

## Product Classification

<b>Product Series</b>	NGF
<b>Product Type</b>	Fiber patch block, with IFC cable
<b>Regional Availability</b>	EMEA   Latin America   North America

## Construction Materials

<b>Fiber Mode</b>	Singlemode
<b>Finish</b>	Powder coated
<b>Material Type</b>	Steel

## Dimensions

<b>Cable Stub Length</b>	20 m   66 ft
<b>Depth</b>	434.34 mm   17.10 in
<b>Height</b>	239.27 mm   9.42 in
<b>Width</b>	153.42 mm   6.04 in

## Environmental Specifications

<b>Operating Temperature</b>	-5 °C to +50 °C (+23 °F to +122 °F)
<b>Qualification Standards</b>	Telcordia GR-449-CORE
<b>Relative Humidity</b>	Up to 80%, non-condensing
<b>Storage Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)

## General Specifications

<b>Shelf Movement</b>	Fixed
<b>Application</b>	Used in NGF-style frames only
<b>Body Style</b>	Left orientation
<b>Cable Stub Type</b>	IFC
<b>Color</b>	Putty white
<b>Color, front</b>	Putty white

<b>Door Type, front</b>	Compression latch   Hinged
<b>Functionality</b>	Patching
<b>Growth Configuration</b>	Fully loaded
<b>Interface Feature, front</b>	APC
<b>Interface, front</b>	SC
<b>Interface, rear</b>	Stub tail
<b>Package Quantity</b>	1
<b>Rack Type</b>	NGF
<b>Total Ports, quantity</b>	96

## Mechanical Specifications

<b>Cable Exit Location</b>	Upward
----------------------------	--------

## Regulatory Compliance/Certifications

**Agency**  
RoHS 2011/65/EU

**Classification**  
Compliant

