



OFDC-A4 Fiber Optic Splice/Patch Closure, gel cable sealing, 2 pre-installed 24-fiber splice trays, no splitter, no adapters

- Advanced gel sealing technology ensures fast and easy field handling without a need for special tools
- Individual access to drop cable connection area and separate zones for looped cable storage for micro-sheet cables only
- Compact and modular design suited for wraparound drop cable installation, enabling faster deployments
- Allows easy pass-through cabling and integration of optical components, even at later deployment stages

Product Classification

Product Type	Single-ended, rectangular fiber closure
Regional Availability	EMEA
Product Series	OFDC

General Specifications

Port, quantity	0
Splicing Type, Supported	Single fusion
Port Type	No adapter
Cable Capacity, Drop	4 Flat 8.0 x 4.5 mm (0.30 x 0.17 in) 4 Round 0–6.0 mm (0–0.23 in) 8 Round 0–4.5 mm (0–0.17 in)
Cable Capacity, Feeder	2 Round 4.5–12.0 mm (0.17–0.47 in)
Distribution Type	0 ports
Enclosure Color	Black
Package, quantity	1
Packaging Type	Box Carton
Splice Protector Length, maximum	45.00 mm 1.77 in
Splice Tray Included, quantity	2
Splice Tray Type Included	24-way, heat shrink
Splicing Capacity, maximum	48

Dimensions

Height	70.00 mm 2.76 in
Length	211.00 mm 8.31 in
Weight	0.55 kg 1.21 lb
Width	94.00 mm 3.70 in

Mechanical Specifications

Cable Sealing Type	Compressed gel
---------------------------	----------------

Enclosure Material Type Rugged polymer
Mount Type Manhole | Pedestal | Strand | Wall

Environmental Specifications

Environmental Space Above ground | Below ground
Installation Temperature -5 °C to +45 °C (+23 °F to +113 °F)
Qualification Standard IEC 60529, IP68 + 2 m waterhead
Relative Humidity 93%, non-condensing
Storage Temperature -30 °C to +60 °C (-22 °F to +140 °F)
UV Resistance UV stabilized

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

