



Next Generation Frame (NGF) Fiber Termination Block with Trunk Cable, LSZH rated, singlemode, OS2, 288 LC/UPC to Stub tail, left oriented, upward cable exit, black, 50 m

## Product Classification

|                              |                                      |
|------------------------------|--------------------------------------|
| <b>Product Series</b>        | NGFB                                 |
| <b>Product Type</b>          | Fiber patch block, with IFC cable    |
| <b>Regional Availability</b> | EMEA   Latin America   North America |

## Construction Materials

|                      |               |
|----------------------|---------------|
| <b>Fiber Mode</b>    | Singlemode    |
| <b>Fiber Type</b>    | OS2           |
| <b>Finish</b>        | Powder coated |
| <b>Material Type</b> | Steel         |

## Dimensions

|                          |               |
|--------------------------|---------------|
| <b>Cable Stub Length</b> | 50 m   164 ft |
|--------------------------|---------------|

## Environmental Specifications

|                                |                                      |
|--------------------------------|--------------------------------------|
| <b>Operating Temperature</b>   | -5 °C to +50 °C (+23 °F to +122 °F)  |
| <b>Qualification Standards</b> | Telcordia GR-449-CORE                |
| <b>Relative Humidity</b>       | Up to 80%, non-condensing            |
| <b>Storage Temperature</b>     | -40 °C to +70 °C (-40 °F to +158 °F) |

## General Specifications

|                                 |                               |
|---------------------------------|-------------------------------|
| <b>Shelf Movement</b>           | Fixed                         |
| <b>Application</b>              | Used in NGF-style frames only |
| <b>Body Style</b>               | Left orientation              |
| <b>Cable Stub Type</b>          | IFC                           |
| <b>Color</b>                    | Black                         |
| <b>Color, front</b>             | Black                         |
| <b>Door Type, front</b>         | Compression latch   Hinged    |
| <b>Functionality</b>            | Patching                      |
| <b>Growth Configuration</b>     | Fully loaded                  |
| <b>Interface Feature, front</b> | Standard                      |
| <b>Interface, front</b>         | LC                            |

|                              |           |
|------------------------------|-----------|
| <b>Interface, rear</b>       | Stub tail |
| <b>Package Quantity</b>      | 1         |
| <b>Rack Type</b>             | NGF       |
| <b>Total Ports, quantity</b> | 288       |

## Mechanical Specifications

|                            |        |
|----------------------------|--------|
| <b>Cable Exit Location</b> | Upward |
|----------------------------|--------|

## Regulatory Compliance/Certifications

**Agency**  
RoHS 2011/65/EU

**Classification**  
Compliant

