



OFDC-A4 Fiber Optic Splice/Patch Closure, gel cable sealing, 2 pre-installed 12-fiber splice trays, no adapters, no splitter

- Advanced gel sealing technology ensures fast and easy field handling without a need for special tools
- Individual access to drop cable connection area and separate zones for looped cable storage for micro-sheet cables only
- Compact and modular design suited for wraparound drop cable installation, enabling faster deployments
- Allows easy pass-through cabling and integration of optical components, even at later deployment stages

## Product Classification

<b>Product Type</b>	Single-ended, rectangular fiber closure
<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Product Series</b>	OFDC

## General Specifications

<b>Port, quantity</b>	0
<b>Splicing Type, Supported</b>	Single fusion
<b>Port Type</b>	No adapter
<b>Cable Capacity, Drop</b>	4 Flat 8.0 x 4.5 mm (0.30 x 0.17 in)   4 Round 0–6.0 mm (0–0.23 in)   8 Round 0–4.5 mm (0–0.17 in)
<b>Cable Capacity, Feeder</b>	2 Round 4.5–12.0 mm (0.17–0.47 in)
<b>Distribution Type</b>	0 ports
<b>Enclosure Color</b>	Black
<b>Package, quantity</b>	1
<b>Packaging Type</b>	Box   Carton
<b>Splice Protector Length, maximum</b>	45.00 mm   1.77 in
<b>Splice Tray Included, quantity</b>	2
<b>Splice Tray Type Included</b>	12-way, heat shrink
<b>Splicing Capacity, maximum</b>	24

## Dimensions

<b>Height</b>	70.00 mm   2.76 in
<b>Length</b>	211.00 mm   8.31 in
<b>Weight</b>	0.55 kg   1.21 lb
<b>Width</b>	94.00 mm   3.70 in

## Mechanical Specifications

<b>Cable Sealing Type</b>	Compressed gel
---------------------------	----------------

**Enclosure Material Type** Rugged polymer  
**Mount Type** Manhole | Pedestal | Strand | Wall

## Environmental Specifications

**Environmental Space** Above ground | Below ground  
**Installation Temperature** -5 °C to +45 °C (+23 °F to +113 °F)  
**Qualification Standard** IEC 60529, IP68 + 2 m waterhead  
**Relative Humidity** 93%, non-condensing  
**Storage Temperature** -30 °C to +60 °C (-22 °F to +140 °F)  
**UV Resistance** UV stabilized

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

