

CF141-50 Jumper with interface types 7-16 DIN Female Panel Mount and SMA Female, 0.3 m



Product Classification

Product Series CF141-50
Product Type Braided cable assembly

General Specifications

Body Style, Connector A Panel mount
Body Style, Connector B Straight
Interface, Connector A 7-16 DIN Female
Interface, Connector B SMA Female
Length 0.300 m | 0.984 ft
Nominal Size 0.141 in
Specification Sheet Revision Level A

Electrical Specifications

DTF, Connector A -28.00 dB
DTF, Connector B -28.00 dB

Jumper Assembly Sample Label

Batch 0123456789 **Manufacturing Date** (two digit year and week) US22 1240 **Product Revision** /A

Manufacturing Plant

Part Number F4-DMDM-2M-D

2 M (6.562 FT)
SUREFLEX ASSEMBLY
U.S. PATENT 5802710
Product of UNITED STATES

Serial Number 12US220001242

Regulatory Compliance/Certifications

Agency

ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system

