

# 244813-1M5



CNT-240 CNT® Jumper with interface types N Male and N Female, 1.5 m

## Product Classification

<b>Brand</b>	CNT®
<b>Product Series</b>	CNT-240
<b>Product Type</b>	Braided cable assembly

## General Specifications

<b>Body Style, Connector A</b>	Straight
<b>Body Style, Connector B</b>	Straight
<b>Interface, Connector A</b>	N Male
<b>Interface, Connector B</b>	N Female
<b>Length</b>	1.500 m   4.921 ft
<b>Nominal Size</b>	0.240 in
<b>Specification Sheet Revision Level</b>	A

## Electrical Specifications

<b>DTF, Connector A</b>	-28.00 dB
<b>DTF, Connector B</b>	-21.00 dB

## Jumper Assembly Sample Label

The label contains the following information:

- Batch:** 0123456789
- Manufacturing Date (two digit year and week):** US22 1240
- Manufacturing Plant:** US22
- Product Revision:** /A
- Part Number:** F4-DMDM-2M-D
- Serial Number:** 12US220001242

Other text on the label includes: COMMSCOPE® Andrew Solutions™, 2 M (6.562 FT), SUREFLEX ASSEMBLY, U.S. PATENT 5802710, and Product of UNITED STATES.

# 244813-1M5

---

## Return Loss/VSWR

### Frequency Band

0–2100 MHz

## Regulatory Compliance/Certifications

### Agency

ISO 9001:2015

### Classification

Designed, manufactured and/or distributed under this quality management system



## Included Products

CNT-240 — CNT-240, CNT® 50 Ohm Braided Coaxial Cable, black PE jacket

240PTM-CR — TNC Male for CNT-240 braided cable

240BPNM-C-CR — Type N Male for CNT-240 braided cable