

# C100-PSMSB-M8



CNT-100 CNT® Jumper with interface types SMA Male and SMB Male, 0.8 m

## Product Classification

Brand	CNT®
Product Series	CNT-100
Product Type	Braided cable assembly

## General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Interface, Connector A	SMA Male
Interface, Connector B	SMB Male
Length	0.800 m   2.625 ft
Nominal Size	0.100 in
Specification Sheet Revision Level	A

## Jumper Assembly Sample Label

Batch: 0123456789  
Manufacturing Date (two digit year and week): US22 1240  
Manufacturing Plant: US22  
Product Revision: /A

COMMScope® Andrew Solutions™  
**F4-DMDM-2M-D** — Part Number  
2 M (6.562 FT)  
SUREFLEX ASSEMBLY  
U.S. PATENT 5802710  
Product of UNITED STATES  
Serial Number: 12US220001242

Barcode: 12US220001242

## Return Loss/VSWR

Frequency Band	VSWR	Return Loss (dB)
700–3000 MHz	1.43	15.00

# C100-PSMSB-M8

---

## Regulatory Compliance/Certifications

**Agency**

ISO 9001:2015

**Classification**

Designed, manufactured and/or distributed under this quality management system



## Included Products

100PSBM-CR — SMB Male (= Female pin) for CNT-100 braided cable

100PSM-CR — SMA Male for CNT-100 braided cable

CNT-100-FR — CNT-100-FR, CNT® 50 Ohm Braided Coaxial Cable, black non-halogenated, fire retardant polyolefin jacket