

# C100-SMSR



CNT-100 CNT® Jumper with interface types SMA Male and SMA Male Right Angle, variable length

## Product Classification

Brand	CNT®
Product Series	CNT-100
Product Type	Braided cable assembly

## General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Right angle
Interface, Connector A	SMA Male
Interface, Connector B	SMA Male
Length	0.000 m   0.000 ft
Nominal Size	0.100 in
Specification Sheet Revision Level	A
Variable Length	For custom lengths contact 828-324-2200 or 1-800-982-1708 (toll free), or your local CommScope representative

## Jumper Assembly Sample Label

The label contains the following information:

- Batch:** 0123456789
- Manufacturing Date (two digit year and week):** US22 1240
- Manufacturing Plant:** US22
- Product Revision:** /A
- Part Number:** F4-DMDM-2M-D
- Serial Number:** 12US220001242

Other text on the label includes: COMMScope Andrew Solutions™, 2 M (6.562 FT), SUREFLEX ASSEMBLY, U.S. PATENT 5802710, Product of UNITED STATES, and a barcode.

## Return Loss/VSWR

Frequency Band	VSWR	Return Loss (dB)
----------------	------	------------------

# C100-SMSR

---

700–3000 MHz

1.43

15.00

## Regulatory Compliance/Certifications

**Agency**

ISO 9001:2015

**Classification**

Designed, manufactured and/or distributed under this quality management system



## Included Products

CNT-100-FR — CNT-100-FR, CNT® 50 Ohm Braided Coaxial Cable, black non-halogenated, fire retardant polyolefin jacket