

C195-NFTM

700–3000 MHz

1.43

15.00

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

ISO 9001:2015

China RoHS SJ/T 11364-2014

Classification

Compliant by Exemption

Designed, manufactured and/or distributed under this quality management system

Above Maximum Concentration Value (MCV)



Included Products

195PNF-CR — Type N Female for CNT-195 braided cable

195PTM — TNC Male for CNT-195 braided cable

CNT-195-FR — CNT-195-FR, CNT® 50 Ohm Braided Coaxial Cable, black non-halogenated, fire retardant polyolefin jacket, Dca s2 d2 Compliant

CNT-195-P — CNT-195, CNT® 50 Ohm Braided Coaxial Cable, white plenum CMP(ETL) C(ETL), fire retardant.

419001003/10 | CNT-195-P-6G — CNT-195, CNT® 50 Ohm Braided Coaxial Cable, white plenum CMP(ETL) C(ETL), fire retardant.