

C100-PSMSB-3M



CNT-100 CNT® Jumper with interface types SMA Male and SMB Male, 3 m

Product Classification

Brand	CNT®
Product Series	CNT-100
Product Type	Braided cable assembly

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Interface, Connector A	SMA Male
Interface, Connector B	SMB Male
Length	3.000 m 9.843 ft
Nominal Size	0.100 in
Specification Sheet Revision Level	A

Jumper Assembly Sample Label

Batch 0123456789 **Manufacturing Date** (two digit year and week) US22 1240 **Product Revision** /A

Part Number F4-DMDM-2M-D

2 M (6.562 FT)
SUREFLEX ASSEMBLY
U.S. PATENT 5802710
Product of UNITED STATES

Serial Number 12US220001242

COMMScope® Andrew Solutions™



Return Loss/VSWR

Frequency Band	VSWR	Return Loss (dB)
700–3000 MHz	1.43	15.00

C100-PSMSB-3M

Regulatory Compliance/Certifications

Agency

ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system



Included Products

100PSBM-CR — SMB Male (= Female pin) for CNT-100 braided cable

100PSM-CR — SMA Male for CNT-100 braided cable

CNT-100-FR — CNT-100-FR, CNT® 50 Ohm Braided Coaxial Cable, black non-halogenated, fire retardant polyolefin jacket