

C141-KFKF-M35



CF141 Jumper with interface types 4.1/9.5 PM Female and 4.1/9.5 PM Female, 0.35 m

Product Classification

Product Series CF141-50
Product Type Braided cable assembly

General Specifications

Body Style, Connector A Straight
Body Style, Connector B Straight
Interface, Connector A 4.3-10 Female
Interface, Connector B 4.3-10 Female
Length 0.350 m | 1.148 ft
Nominal Size 0.141 in
Specification Sheet Revision Level A

Electrical Specifications

3rd Order IMD -112.00 dBm

Jumper Assembly Sample Label

The label contains the following information:

- Batch:** 0123456789
- Manufacturing Date (two digit year and week):** US22 1240
- Manufacturing Plant:** US22
- Product Revision:** /A
- Part Number:** F4-DMDM-2M-D
- Serial Number:** 12US220001242

Other text on the label includes: COMMScope Andrew Solutions™, 2 M (6.562 FT), SUREFLEX ASSEMBLY, U.S. PATENT 5802710, Product of UNITED STATES, and a barcode.

Return Loss/VSWR

Frequency Band

700–3000 MHz

VSWR

1.12

Return Loss (dB)

25.00

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

ISO 9001:2015

China RoHS SJ/T 11364-2014

Classification

Compliant by Exemption

Designed, manufactured and/or distributed under this quality management system

Above Maximum Concentration Value (MCV)

