



Undercarpet Flat Copper Cable, 3 conductors, 12 AWG, shielded, 250 ft, white/green/black

- Available in 3 and 5-conductor versions
- Undercarpet cable with isolated ground is for use with sensitive computer equipment

Product Classification

| | |
|------------------------------|---------------|
| Product Series | Undercarpet |
| Product Type | Power cable |
| Regional Availability | North America |

Construction Materials

| | |
|----------------------------|-------------|
| Conductor Material | Bare copper |
| Insulation Material | PVC |

Dimensions

| | |
|---------------------------|----------------------|
| Cable Length | 76 m 250 ft |
| Height Over Jacket | 1.300 mm 0.051 in |
| Width Over Jacket | 70.570 mm 2.778 in |

Electrical Specifications

| | |
|--------------------------------|----------------|
| Current Rating, maximum | 20.0 A @ 20 °C |
| Safety Voltage Rating | 300 V |

Environmental Specifications

| | |
|----------------------------|----------|
| Environmental Space | Indoor |
| Safety Standard | CSA UL |

General Specifications

| | |
|---------------------------------|----------|
| Cable Type | FCC |
| Conductor Gauge, singles | 12 AWG |
| Conductors, quantity | 3 |
| Ground Wire Type | Standard |
| Jacket Color | Blue |

3-553079-1

Jacket Color, singles Black | Green | White
Packaging Type Reel

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

