



Undercarpet Flat Copper Cable, 3 conductors, 12 AWG, shielded, 50 ft, white/green/black

- Undercarpet cable with isolated ground is for use with sensitive computer equipment
- Available in 3 and 5-conductor versions

Product Classification

Product Series	Undercarpet
Product Type	Power cable
Regional Availability	North America

Construction Materials

Conductor Material	Bare copper
Insulation Material	PVC

Dimensions

Cable Length	15 m 50 ft
Height Over Jacket	1.300 mm 0.051 in
Width Over Jacket	70.570 mm 2.778 in

Electrical Specifications

Current Rating, maximum	20.0 A @ 20 °C
Safety Voltage Rating	300 V

Environmental Specifications

Environmental Space	Indoor
Safety Standard	CSA UL

General Specifications

Cable Type	FCC
Conductor Gauge, singles	12 AWG
Conductors, quantity	3
Ground Wire Type	Standard
Jacket Color	Blue

3-553079-3

Jacket Color, singles Black | Green | White
Packaging Type Reel

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

