



Undercarpet Flat Copper Cable, 5 conductors, 12 AWG, shielded, 250 ft, white/green/black/blue/red

- Available in 3 and 5-conductor versions

## Product Classification

<b>Product Series</b>	Undercarpet
<b>Product Type</b>	Power cable
<b>Regional Availability</b>	North America

## Construction Materials

<b>Conductor Material</b>	Bare copper
<b>Insulation Material</b>	PVC

## Dimensions

<b>Cable Length</b>	76 m   250 ft
<b>Height Over Jacket</b>	0.870 mm   0.034 in
<b>Width Over Jacket</b>	117.348 mm   4.620 in

## Electrical Specifications

<b>Current Rating, maximum</b>	20.0 A @ 20 °C
<b>Safety Voltage Rating</b>	300 V

## Environmental Specifications

<b>Environmental Space</b>	Indoor
<b>Safety Standard</b>	CSA   UL

## General Specifications

<b>Cable Type</b>	FCC
<b>Conductor Gauge, singles</b>	12 AWG
<b>Conductors, quantity</b>	5
<b>Ground Wire Type</b>	Standard
<b>Jacket Color</b>	Blue

# 3-553239-1

---

**Jacket Color, singles**      Black | Blue | Green | Red | White  
**Packaging Type**              Reel

## Regulatory Compliance/Certifications

**Agency**  
RoHS 2011/65/EU

**Classification**  
Compliant

