



Undercarpet Flat Copper Cable, 5 conductors, 12 AWG, shielded, 100 ft, white/green/black/blue/red

- Available in 3 and 5-conductor versions

Product Classification

Product Series	Undercarpet
Product Type	Power cable
Regional Availability	North America

Construction Materials

Conductor Material	Bare copper
Insulation Material	PVC

Dimensions

Cable Length	30 m 100 ft
Height Over Jacket	0.870 mm 0.034 in
Width Over Jacket	117.348 mm 4.620 in

Electrical Specifications

Current Rating, maximum	20.0 A @ 20 °C
Safety Voltage Rating	300 V

Environmental Specifications

Environmental Space	Indoor
Safety Standard	CSA UL

General Specifications

Cable Type	FCC
Conductor Gauge, singles	12 AWG
Conductors, quantity	5
Ground Wire Type	Standard
Jacket Color	Blue

3-553239-4

Jacket Color, singles Black | Blue | Green | Red | White

Packaging Type Reel

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant

