



Undercarpet Flat Copper Cable, 3 conductors, 12 AWG, shielded, 100 ft, white/green/black

- Available in 3 and 5-conductor versions
- Undercarpet cable with isolated ground is for use with sensitive computer equipment

Product Classification

Product Series	Undercarpet
Product Type	Power cable
Regional Availability	North America

Construction Materials

Conductor Material	Bare copper
Insulation Material	PVC

Dimensions

Cable Length	30 m 100 ft
Height Over Jacket	1.300 mm 0.051 in
Width Over Jacket	70.570 mm 2.778 in

Electrical Specifications

Current Rating, maximum	20.0 A @ 20 °C
Safety Voltage Rating	300 V

Environmental Specifications

Environmental Space	Indoor
Safety Standard	CSA UL

General Specifications

Cable Type	FCC
Conductor Gauge, singles	12 AWG
Conductors, quantity	3
Ground Wire Type	Standard
Jacket Color	Blue

3-553079-4

Jacket Color, singles Black | Green | White
Packaging Type Reel

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

