

# PWR-806-SE-105 M



HELIAX® FiberFeed® Remote Radio Head Power Cable, 8 conductor, 6 AWG, four Blue and four Grey 105 meter

## Product Classification

<b>Portfolio</b>	CommScope®
<b>Brand</b>	FiberFeed®   HELIAX®
<b>Product Type</b>	Power cable
<b>Regional Availability</b>	Europe

## Construction Materials

<b>Jacket Material</b>	PVC
------------------------	-----

## Dimensions

<b>Cable Length</b>	105 m   344 ft
<b>Cable Weight</b>	151.70 kg/m
<b>Diameter Over Jacket, nominal</b>	29.100 mm   1.146 in

## Electrical Specifications

<b>Conductor dc Resistance</b>	0.41 ohms/kft
<b>Conductor dc Resistance Note</b>	Maximum value based on a standard condition of 20 °C (68 °F)

## Environmental Specifications

<b>Installation Temperature</b>	-30 °C to +70 °C (-22 °F to +158 °F)
<b>Operating Temperature</b>	-40 °C to +80 °C (-40 °F to +176 °F)
<b>Storage Temperature</b>	-40 °C to +85 °C (-40 °F to +185 °F)

## General Specifications

<b>Conductor Gauge, singles</b>	6 AWG
<b>Conductors, quantity</b>	8

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

