



M81 BNC-B Coupler 50 Ohm

## Product Classification

<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Multimedia coupler
<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America

## General Specifications

<b>Application</b>	Module designed for data applications
<b>Mount Type</b>	Snap-in
<b>Package Quantity</b>	1

## Dimensions

<b>Depth</b>	15.24 mm   0.60 in
<b>Height</b>	17.53 mm   0.69 in
<b>Width</b>	18.54 mm   0.73 in

## Environmental Specifications

<b>Operating Temperature</b>	-10 °C to +60 °C (+14 °F to +140 °F)
<b>Relative Humidity</b>	5%–95%, non-condensing
<b>Storage Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

