



M81 RCA to 110 Punchdown Module Audio and Video Adapter, white housing white connector

Product Classification

| | |
|------------------------------|---|
| Portfolio | CommScope® |
| Product Type | Multimedia outlet |
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |

General Specifications

| | |
|-------------------------|---------|
| Color | White |
| Color, RCA | White |
| Mount Type | Snap-in |
| Package Quantity | 1 |

Mechanical Specifications

| | |
|----------------------|---|
| Material Type | High-impact, flame retardant, thermoplastic |
|----------------------|---|

Electrical Specifications

| | |
|---------------------------------------|------------------|
| Attenuation dc, maximum | 2 dB @ 5.5 MHz |
| Crosstalk | -60 dB @ 5.5 MHz |
| Impedance | 75 ohm |
| Insulation Resistance, minimum | 50 MOhm |
| UTP 110 Terminal Block | 110 ohm |

Environmental Specifications

| | |
|------------------------------|--------------------------------------|
| Flammability Rating | UL 94 V-0 |
| Operating Temperature | -10 °C to +60 °C (+14 °F to +140 °F) |
| Relative Humidity | 5%–95%, non-condensing |
| Storage Temperature | -40 °C to +70 °C (-40 °F to +158 °F) |

Regulatory Compliance/Certifications

| Agency | Classification |
|-----------------|--|
| RoHS 2011/65/EU | Compliant |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |

