



## GigaSPEED XL® PATCHMAX® GS3 Category 6 U/UTP 2U Panel Kit

## Product Classification

<b>Portfolio</b>	SYSTIMAX®
<b>Brand</b>	GigaSPEED XL®   PATCHMAX®
<b>Product Type</b>	RJ45 patch panel
<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America

## Dimensions

<b>Depth, with cable management</b>	206.50 mm   8.13 in
<b>Height</b>	89.66 mm   3.53 in
<b>Width</b>	482.60 mm   19.00 in

## Electrical Specifications

<b>ANSI/TIA Category</b>	6
--------------------------	---

## Environmental Specifications

<b>Flammability Rating</b>	UL 94 V-0
<b>Operating Temperature</b>	-10 °C to +60 °C (+14 °F to +140 °F)
<b>Relative Humidity</b>	Up to 95%, non-condensing
<b>Safety Standard</b>	cUL   UL
<b>Storage Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)

## General Specifications

<b>Intelligence Type</b>	Passive
<b>Cable Type</b>	Unshielded
<b>Color</b>	Black
<b>Package Quantity</b>	1
<b>Rack Type</b>	EIA 19 in
<b>Rack Units</b>	2.0

## Mechanical Specifications

<b>Material Type</b>	High-impact, flame retardant, thermoplastic   Powder-coated steel
----------------------	---

## Regulatory Compliance/Certifications

### Agency

RoHS 2011/65/EU  
ISO 9001:2015

### Classification

Compliant  
Designed, manufactured and/or distributed under this quality management system

