



SYSTIMAX 360™ iPatch® G2 Fixed Fiber Panel with InstaPATCH 360 LazrSPEED Modules

Product Classification

| | |
|------------------------------|---|
| Portfolio | SYSTIMAX® |
| Brand | iPatch® SYSTIMAX 360™ |
| Product Type | Fiber splice panel |
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |

Construction Materials

| | |
|----------------------|--|
| Fiber Mode | Multimode |
| Material Type | Acrylonitrile butadiene styrene (ABS) Polycarbonate (PC) |

Dimensions

| | |
|---------------|----------------------|
| Depth | 355.60 mm 14.00 in |
| Height | 44.45 mm 1.75 in |
| Width | 482.60 mm 19.00 in |
| Weight | 2.95 kg 6.50 lb |

Environmental Specifications

| | |
|------------------------------|--------------------------------------|
| Flammability Rating | UL 94 V-0 |
| Operating Temperature | -5 °C to +50 °C (+23 °F to +122 °F) |
| Relative Humidity | Up to 95%, non-condensing |
| Safety Standard | Austel CE CSA UL |
| Storage Temperature | -40 °C to +70 °C (-40 °F to +158 °F) |

General Specifications

| | |
|------------------------------|-----------------|
| Intelligence Type | iPatch® enabled |
| Rack Units | 1.0 |
| Shelf Movement | Fixed |
| Color | Black |
| Interface, front | LC |
| Package Quantity | 1 |
| Total Ports, quantity | 24 |

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU
ISO 9001:2015

Classification

Compliant
Designed, manufactured and/or distributed under this quality management system

