



SYSTIMAX 360™ GigaSPEED XL® PATCHMAX® GS3 Distribution Module

Product Classification

Portfolio	SYSTIMAX®
Brand	GigaSPEED XL® PATCHMAX® SYSTIMAX 360™
Product Type	Module
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Dimensions

Diameter Over Dielectric, maximum	1.168 mm 0.046 in
Diameter Over Dielectric, minimum	0.762 mm 0.030 in

Electrical Specifications

ANSI/TIA Category	6
Current Rating	1.5 A @ 20 °C 1.5 A @ 68 °F
Dielectric Withstand Voltage, RMS, conductive surface	1500 Vac @ 60 Hz
Dielectric Withstand Voltage, RMS, contact-to-contact	1000 Vac @ 60 Hz
Insulation Resistance, minimum	500 MOhm

Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Relative Humidity	Up to 95%, non-condensing
Safety Standard	cUL UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

Intelligence Type	iPatch® ready
Total Ports, quantity	6
Cable Type	Unshielded
Color	Cool gray
Modules, quantity	1
Package Quantity	1

Mechanical Specifications

Conductor Gauge, solid	22 AWG 24 AWG
Conductor Gauge, stranded	22 AWG 24 AWG
Conductor Type	Solid Stranded
Contact Plating Material	Precious metals
Material Type	High-impact, flame retardant, thermoplastic
Plug Insertion Life, minimum	750 times
Plug Insertion Life, test plug	IEC 60603-7 compliant plug
Plug Retention Force, minimum	30 lbf 133 N
Termination Contact Plating	Nickel
Termination Type	IDC
Wiring	T568A T568B

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

