


SYSTIMAX 360™ PATCHMAX® Panel Kit, 2U, 24 port



Product Classification

Portfolio	SYSTIMAX®
Brand	GigaSPEED X10D®
Product Type	RJ45 patch panel
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Dimensions

Depth, with cable management	266.70 mm 10.50 in
Height	88.90 mm 3.50 in
Width	482.60 mm 19.00 in

Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Relative Humidity	Up to 95%, non-condensing
Safety Standard	cUL UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

Intelligence Type	iPatch® ready
Total Ports, quantity	24
Cable Type	Unshielded
Color	Cool gray Satin chrome
Package Quantity	1
Rack Type	EIA 19 in
Rack Units	2.0

Mechanical Specifications

Material Type	High-impact, flame retardant, thermoplastic Powder-coated steel
----------------------	---

Regulatory Compliance/Certifications

Agency	Classification
--------	----------------

RoHS 2011/65/EU
ISO 9001:2015

Compliant
Designed, manufactured and/or distributed under this quality management system

