



360G2 Cassette 12 LC Singlemode Blue with Pigtails iPatch Ready

Product Classification

Portfolio	CommScope®
Product Type	Fiber cassette with pigtails
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Construction Materials

Fiber Type	G.652.D and G.657.A1 , TeraSPEED® OS2
Total Fibers, quantity	12

Dimensions

Depth	119.38 mm 4.70 in
Height	30.48 mm 1.20 in
Pigtail Length	1.5 m 4.9 ft
Width	91.44 mm 3.60 in

Environmental Specifications

Safety Standard	UL
------------------------	----

General Specifications

Interface, front	LC
Adapter Color	Blue
Intelligence Type	iPatch® ready
Interface Feature, front	Standard
Package Quantity	1
Total Ports, quantity, front	12

Optical Performance

Insertion Loss, typical	0.30 dB
Return Loss, minimum	55.0 dB

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU
ISO 9001:2015

Classification

Compliant
Designed, manufactured and/or distributed under this quality management system



Included Products

860278613 (Product Component—not orderable) — TeraSPEED® LC 0.9 mm Pigtail, blue, 1.5 m

- 760095596 | X-TB-8W-BL-F/G (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber
- 460125289 (Product Component—not orderable) — Behind The Wall Pre-Radiused LC Connector for 0.9 mm Fiber, single-mode
- 760211201 | X-TB-8G-BL-F/G (Product Component—not orderable) — 900µm Tight Buffered Fiber

860278621 (Product Component—not orderable) — TeraSPEED® LC 0.9 mm Pigtail, orange, 1.5 m

- 760095604 | X-TB-8W-OR-F/G (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber
- 460125289 (Product Component—not orderable) — Behind The Wall Pre-Radiused LC Connector for 0.9 mm Fiber, single-mode
- 760211219 | X-TB-8G-OR-F/G (Product Component—not orderable) — 900µm Tight Buffered Fiber

860278639 (Product Component—not orderable) — TeraSPEED® LC 0.9 mm Pigtail, green, 1.5 m

- 760095612 | X-TB-8W-GR-F/G (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber
- 460125289 (Product Component—not orderable) — Behind The Wall Pre-Radiused LC Connector for 0.9 mm Fiber, single-mode

860278647 (Product Component—not orderable) — TeraSPEED® LC 0.9 mm Pigtail, brown, 1.5 m

- 760095620 | X-TB-8W-BR-F/G (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber
- 460125289 (Product Component—not orderable) — Behind The Wall Pre-Radiused LC Connector for 0.9 mm Fiber, single-mode

860278654 (Product Component—not orderable) — TeraSPEED® LC 0.9 mm Pigtail, slate, 1.5 m

- 760095638 | X-TB-8W-SL-F/G (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber
- 460125289 (Product Component—not orderable) — Behind The Wall Pre-Radiused LC Connector for 0.9 mm Fiber, single-mode

860278662 (Product Component—not orderable) — TeraSPEED® LC 0.9 mm Pigtail, white, 1.5 m

- 760095646 | X-TB-8W-WH-F/G (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber
- 460125289 (Product Component—not orderable) — Behind The Wall Pre-Radiused LC Connector for 0.9 mm Fiber, single-mode

860278670 (Product Component—not orderable) — TeraSPEED® LC 0.9 mm Pigtail, red, 1.5 m

- 760095653 | X-TB-8W-RD-F/G (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber
- 460125289 (Product Component—not orderable) — Behind The Wall Pre-Radiused LC Connector for 0.9 mm Fiber, single-mode

760109496 | 360G2 Cassette 12-LC-SM-BL-Pigtails

- 860278688 (Product Component—not orderable) — TeraSPEED® LC 0.9 mm Pigtail, black, 1.5 m
- 760095661 | X-TB-8W-BK-F/G (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber
 - 460125289 (Product Component—not orderable) — Behind The Wall Pre-Radiused LC Connector for 0.9 mm Fiber, single-mode
- 860278696 (Product Component—not orderable) — TeraSPEED® LC 0.9 mm Pigtail, yellow, 1.5 m
- 760038570 | X-TB-8W-YL-F/G (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber
 - 460125289 (Product Component—not orderable) — Behind The Wall Pre-Radiused LC Connector for 0.9 mm Fiber, single-mode
 - 760200568 | X-TB-8G-YL-F/G (Product Component—not orderable) — 900µm Tight Buffered Fiber
- 860278704 (Product Component—not orderable) — TeraSPEED® LC 0.9 mm Pigtail, violet, 1.5 m
- 760095679 | X-TB-8W-VI-F/G (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber
 - 460125289 (Product Component—not orderable) — Behind The Wall Pre-Radiused LC Connector for 0.9 mm Fiber, single-mode
- 860278712 (Product Component—not orderable) — TeraSPEED® LC 0.9 mm Pigtail, rose, 1.5 m
- 760095687 | X-TB-8W-RS-F/G (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber
 - 460125289 (Product Component—not orderable) — Behind The Wall Pre-Radiused LC Connector for 0.9 mm Fiber, single-mode
- 860278720 (Product Component—not orderable) — TeraSPEED® LC 0.9 mm Pigtail, aqua, 1.5 m
- 760095695 | X-TB-8W-AQ-F/G (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber
 - 460125289 (Product Component—not orderable) — Behind The Wall Pre-Radiused LC Connector for 0.9 mm Fiber, single-mode
- 760049809 | SFA-LC12-BL-SHUTTERED — TeraSPEED® LC Multiport Shuttered Adapter, Blue, Single Pack