

## SYSTIMAX 360™ PATCHMAX® Panel Kit, 2U, 48 port



## Product Classification

|                              |   |
|------------------------------|---|
| <b>Portfolio</b>             | SYSTIMAX®   |
| <b>Brand</b>                 | GigaSPEED X10D®   |
| <b>Product Type</b>          | RJ45 patch panel  |
| <b>Regional Availability</b> | Asia   Australia/New Zealand   EMEA   Latin America   North America |

## Dimensions

|                                     |                      |
|-------------------------------------|----------------------|
| <b>Depth, with cable management</b> | 266.70 mm   10.50 in |
| <b>Height</b>                       | 88.90 mm   3.50 in   |
| <b>Width</b>                        | 482.60 mm   19.00 in |

## Environmental Specifications

|                              |                                      |
|------------------------------|--------------------------------------|
| <b>Flammability Rating</b>   | UL 94 V-0                            |
| <b>Operating Temperature</b> | -10 °C to +60 °C (+14 °F to +140 °F) |
| <b>Relative Humidity</b>     | Up to 95%, non-condensing            |
| <b>Safety Standard</b>       | cUL   UL                             |
| <b>Storage Temperature</b>   | -40 °C to +70 °C (-40 °F to +158 °F) |

## General Specifications

|                              |                          |
|------------------------------|--------------------------|
| <b>Intelligence Type</b>     | iPatch® ready            |
| <b>Total Ports, quantity</b> | 48                       |
| <b>Cable Type</b>            | Unshielded               |
| <b>Color</b>                 | Cool gray   Satin chrome |
| <b>Package Quantity</b>      | 1                        |
| <b>Rack Type</b>             | EIA 19 in                |
| <b>Rack Units</b>            | 2.0                      |

## Mechanical Specifications

|                      |   |
|----------------------|---|
| <b>Material Type</b> | High-impact, flame retardant, thermoplastic   Powder-coated steel |
|----------------------|---|

## Regulatory Compliance/Certifications

| Agency | Classification |
|--------|----------------|
|--------|----------------|

RoHS 2011/65/EU  
ISO 9001:2015

Compliant  
Designed, manufactured and/or distributed under this quality management system

