

FlexiMAX U/UTP High Density Patch Panel



Product Classification

Portfolio	SYSTIMAX®
Product Type	RJ45 patch panel
Regional Availability	EMEA

Dimensions

Depth	105.92 mm 4.17 in
Height	43.69 mm 1.72 in
Width	482.60 mm 19.00 in

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Safety Standard	cUL UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

Intelligence Type	Passive
Total Ports, quantity	24
Cable Type	Unshielded
Color	Black
Package Quantity	1
Rack Type	EIA 19 in
Rack Units	1.0

Mechanical Specifications

Material Type	High-impact, flame retardant, thermoplastic Powder-coated steel
----------------------	---

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

