



## SYSTIMAX 360™ Evolve 24-port flat panel

## Product Classification

<b>Portfolio</b>	SYSTIMAX®
<b>Brand</b>	SYSTIMAX 360™
<b>Product Type</b>	RJ45 patch panel
<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America

## Dimensions

<b>Depth</b>	40.64 mm   1.60 in
<b>Depth, with cable management</b>	170.18 mm   6.70 in
<b>Diameter Over Dielectric, maximum</b>	1.168 mm   0.046 in
<b>Diameter Over Dielectric, minimum</b>	0.762 mm   0.030 in
<b>Height</b>	44.45 mm   1.75 in
<b>Weight</b>	0.50 kg   1.10 lb
<b>Width</b>	482.60 mm   19.00 in

## Electrical Specifications

<b>ANSI/TIA Category</b>	5e   6   6A
<b>Current Rating</b>	1.5 A @ 20 °C 1.5 A @ 68 °F
<b>Dielectric Withstand Voltage, RMS, conductive surface</b>	1500 Vac @ 60 Hz
<b>Dielectric Withstand Voltage, RMS, contact-to-contact</b>	1000 Vac @ 60 Hz
<b>Insulation Resistance, minimum</b>	500 MOhm

## Environmental Specifications

<b>Flammability Rating</b>	UL 94 V-0
<b>Operating Temperature</b>	-10 °C to +60 °C (+14 °F to +140 °F)
<b>Relative Humidity</b>	Up to 95%, non-condensing
<b>Safety Standard</b>	cUL   UL
<b>Storage Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)

## General Specifications

<b>Total Ports, quantity</b>	24
------------------------------	----

<b>Cable Type</b>	Unshielded
<b>Color</b>	Cool gray
<b>Label Height</b>	0.43 in
<b>Label Length</b>	1.33 in
<b>Modules, quantity</b>	24
<b>Package Quantity</b>	1
<b>Rack Type</b>	EIA 19 in
<b>Rack Units</b>	1.0

## Mechanical Specifications

<b>Panel Style</b>	Straight
<b>Material Type</b>	High-impact, flame retardant, thermoplastic   Powder-coated steel
<b>Wiring</b>	T568A   T568B

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
RoHS 2011/65/EU	
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

