



## InstaPATCH® 360 Multimode OM4 LS TAP Module, 50:50, 12 LC ports

### Product Classification

<b>Portfolio</b>	SYSTIMAX®
<b>Brand</b>	InstaPATCH® 360
<b>Product Type</b>	Fiber module
<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America

### Construction Materials

<b>Fiber Type</b>	OM4, LazrSPEED® 550
<b>Total Fibers, quantity</b>	12

### Dimensions

<b>Depth</b>	165.10 mm   6.50 in
<b>Height</b>	27.94 mm   1.10 in
<b>Width</b>	91.44 mm   3.60 in

### Environmental Specifications

<b>Safety Standard</b>	UL
------------------------	----

### General Specifications

<b>Interface, front</b>	LC
<b>Total Ports, quantity, front</b>	12
<b>Interface Feature, front</b>	Standard
<b>Color, front</b>	Aqua
<b>Adapters, quantity, front</b>	12
<b>Data Module Type</b>	TAP (Traffic Access Point)
<b>Intelligence Type</b>	iPatch® ready
<b>Shuttered</b>	No
<b>Interface, rear</b>	MPO Male
<b>Adapters, quantity, rear</b>	2
<b>Interface Feature, rear</b>	Reduced footprint
<b>Color, rear</b>	Gray   Red
<b>Package Quantity</b>	1

## Optical Performance

**Insertion Loss, maximum** 4.16 dB

**Tap Insertion Loss, maximum** 4.20 dB

## Regulatory Compliance/Certifications

### Agency

RoHS 2011/65/EU

ISO 9001:2015

### Classification

Compliant

Designed, manufactured and/or distributed under this quality management system

