



SYSTIMAX 360™ iPatch® 32-MPO UHD Shelf, 6PK imVision Upgrade Kit

Product Classification

Portfolio	SYSTIMAX®
Brand	iPatch® LazrSPEED® SYSTIMAX 360™
Product Type	Upgrade kit
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Construction Materials

Fiber Mode	Multimode Singlemode
Material Type	Acrylonitrile butadiene styrene (ABS) Polycarbonate (PC)

Dimensions

Depth	17.78 mm 0.70 in
Height	26.16 mm 1.03 in
Width	194.31 mm 7.65 in
Weight	0.11 kg 0.25 lb

Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-5 °C to +50 °C (+23 °F to +122 °F)
Relative Humidity	Up to 95%, non-condensing
Safety Standard	Austel CE CSA UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

Intelligence Type	iPatch® enabled
Color	Cool gray
Interface	MPO
Package Quantity	6
Total Ports, quantity	192

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

