



SYSTIMAX 360™ iPatch® Upgrade Kit for Evolve Angled Panel, 24 Port, 10 pack

Product Classification

| | |
|------------------------------|---|
| Portfolio | SYSTIMAX® |
| Brand | iPatch® SYSTIMAX 360™ |
| Product Type | RJ45 patch panel |
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |

Dimensions

| | |
|--|---------------------|
| Diameter Over Dielectric, maximum | 1.168 mm 0.046 in |
| Diameter Over Dielectric, minimum | 0.762 mm 0.030 in |
| Weight | 0.11 kg 0.25 lb |

Electrical Specifications

| | |
|--|--------------------------------|
| ANSI/TIA Category | 6 6A |
| Current Rating | 1.5 A @ 20 °C 1.5 A @ 68 °F |
| Dielectric Withstand Voltage, RMS, conductive surface | 1500 Vac @ 60 Hz |
| Dielectric Withstand Voltage, RMS, contact-to-contact | 1000 Vac @ 60 Hz |

Environmental Specifications

| | |
|------------------------------|--------------------------------------|
| Flammability Rating | UL 94 V-0 |
| Operating Temperature | -5 °C to +50 °C (+23 °F to +122 °F) |
| Relative Humidity | Up to 95%, non-condensing |
| Safety Standard | ACMA CE cUL UL |
| Storage Temperature | -40 °C to +70 °C (-40 °F to +158 °F) |

General Specifications

| | |
|------------------------------|---------------------|
| Intelligence Type | iPatch® upgrade kit |
| Total Ports, quantity | 24 |
| Color | Cool gray |
| Package Quantity | 10 |

Mechanical Specifications

| | |
|----------------------|---|
| Panel Style | Angled |
| Material Type | Acrylonitrile butadiene styrene (ABS) Polycarbonate |

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

ISO 9001:2015

Classification

Compliant

Designed, manufactured and/or distributed under this quality management system

