

imVision® Power Supply 12VDC 3050 mm Power Cord



Product Classification

Portfolio	SYSTIMAX®
Brand	imVision®
Product Type	Network controller accessory
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

General Specifications

Package Quantity	1
-------------------------	---

Electrical Specifications

Output Current at Voltage, continuous	2.08 A @ 12 Vdc
--	-----------------

Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	0 °C to +50 °C (+32 °F to +122 °F)
Relative Humidity	Up to 95%, non-condensing
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Safety Standard	C-tick CE cUL GOST KC

Regulatory Compliance/Certifications

Agency	RoHS 2011/65/EU	Classification	Compliant
---------------	-----------------	-----------------------	-----------

