



G2 Multimode OM5 WideBand Module, 24 LC ports

- LazrSPEED® WideBand extends the capability of OM4 across enough spectrum to support at least four low-cost wavelengths

This product will be discontinued on: June 30, 2019

Replaced By

760217950

360DMis-24LC-WB

G2 Multimode OM5 WideBand Module, 24 LC fibers (12 duplex ports)

Product Classification

Portfolio	CommScope®
Product Type	Fiber module
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Construction Materials

Fiber Type	OM5, LazrSPEED® wideband
Total Fibers, quantity	24

Dimensions

Depth	116.84 mm 4.60 in
Height	30.48 mm 1.20 in
Width	91.44 mm 3.60 in

Environmental Specifications

Safety Standard	UL
------------------------	----

General Specifications

Interface, front	LC
Total Ports, quantity, front	24
Interface Feature, front	Standard
Color, front	Lime green
Adapters, quantity, front	24
Data Module Type	WideBand
Intelligence Type	iPatch® ready
Shuttered	Yes
Interface, rear	MPO Pinned

Adapters, quantity, rear	2
Interface Feature, rear	Standard
Color, rear	Gray
Package Quantity	1

Optical Performance

Insertion Loss, maximum 0.47 dB

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



Included Products

CS-5G-MP (Product Component—not orderable) — LazrSPEED® OM5 WideBand Multimode Fiber