

imVision Controller Display (Only)

Product Classification

Portfolio	SYSTIMAX®
Brand	imVision® iPatch®
Product Type	Controller unit
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

General Specifications

Color	Cool gray
Package Quantity	1

Dimensions

Height	81.28 mm 3.20 in
Weight	0.25 kg 0.55 lb

Mechanical Specifications

Material Type	Acrylonitrile butadiene styrene (ABS) Polycarbonate Steel
----------------------	---

Electrical Specifications

Input Voltage	100–240 Vac
----------------------	-------------

Environmental Specifications

Operating Temperature	0 °C to +50 °C (+32 °F to +122 °F)
Relative Humidity	Up to 95%, non-condensing
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Safety Standard	CE RCM UL

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

