



Power Supply Unit, 57 Vdc, 100-240 Vac

Product Classification

Brand Era™ | ION®-E
Product Type Power supply

General Specifications

Note Detailed Product Specifications are available. Please contact your local CommScope representative.

Electrical Specifications

Input Frequency Range 47–66 Hz
Input Voltage Range +85 to +264 Vac
Output Power, maximum 2000 W
Output Voltage 57 Vdc

Supervision And Control

RF Alarm Current failure

Environmental Specifications

Mean Time Between Failures (MTBF) 103 yr @ 25 °C
Operating Temperature -10 °C to +55 °C (+14 °F to +131 °F)

Dimensions

Depth 350.00 mm | 13.78 in
Height 42.00 mm | 1.65 in
Net Weight 2.30 kg | 5.07 lb

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |

