

## ION®-E Wireless Communications Switch Subrack, 2 U



## Product Classification

<b>Brand</b>	Era™   ION®-E
<b>Product Type</b>	Subrack

## General Specifications

<b>Includes</b>	Fan filter   Fan tray
<b>Note</b>	Detailed Product Specifications are available. Please contact your local CommScope representative.
<b>Rack Type</b>	EIA 19 in

## Electrical Specifications

<b>Electrical Safety Standard</b>	EN 60950
<b>Power Consumption</b>	45 W
<b>Voltage Range</b>	12 Vdc

## Mechanical Specifications

<b>Mounting</b>	Rack
<b>Slots Available, quantity</b>	11

## Environmental Specifications

<b>Mean Time Between Failures (MTBF)</b>	45 yr @ 25 °C
<b>Operating Temperature</b>	+5 °C to +40 °C (+41 °F to +104 °F)

## Dimensions

<b>Depth</b>	450.00 mm   17.72 in
<b>Height</b>	88.50 mm   3.48 in
<b>Net Weight</b>	7.60 kg   16.76 lb
<b>Width</b>	482.00 mm   18.98 in

## Packed Dimensions

<b>Depth</b>	185.0 mm   7.3 in
<b>Height</b>	522.0 mm   20.6 in

**Width**

585.0 mm | 23.0 in