



e-POI Subrack with Interface Card

## Product Classification

|                     |               |
|---------------------|---------------|
| <b>Brand</b>        | Era™   ION®-E |
| <b>Product Type</b> | Subrack       |

## General Specifications

|                  |  |
|------------------|--|
| <b>Note</b>      | Detailed Product Specifications are available. Please contact your local CommScope representative. |
| <b>Rack Type</b> | EIA 19 in  |

## Mechanical Specifications

|                                  |      |
|----------------------------------|------|
| <b>Mounting</b>                  | Rack |
| <b>Slots Available, quantity</b> | 8    |

## Environmental Specifications

|  |                                     |
|--|-------------------------------------|
| <b>Mean Time Between Failures (MTBF)</b> | 146 yr @ 25 °C                      |
| <b>Operating Temperature</b>             | -5 °C to +50 °C (+23 °F to +122 °F) |

## Dimensions

|                   |                      |
|-------------------|----------------------|
| <b>Depth</b>      | 395.00 mm   15.55 in |
| <b>Height</b>     | 178.00 mm   7.01 in  |
| <b>Net Weight</b> | 7.70 kg   16.98 lb   |
| <b>Width</b>      | 482.00 mm   18.98 in |