


# SFG22RHDX-11-B



G22RHDX Tower Sector Frame with spine extension for RRU Mounting, 11 ft x 2.88 in OD face pipes. Base Kit Only. No antenna pipes.

- Extended spine for SFG22 RHDX mounts that decrease PIM from radio relocation
- Increased versatility and stability
- Updated frame provides higher loading
- More RRU mounting available, reducing need for additional mounts
- Better load management
- Less structure stress
- Can be used in combination with APEX RRU mounts

## Product Classification

|                       |                                  |
|-----------------------|----------------------------------|
| <b>Product Type</b>   | High capacity Tower sector frame |
| <b>Product Brand</b>  | PIM-guard                        |
| <b>Product Series</b> | G2                               |

## General Specifications

|                          |  |
|--------------------------|--|
| <b>Mounting</b>          | Angle 60°, 203.2 mm (8 in)   Straight or tapered legs up to 203.2 mm (8 in) OD |
| <b>Patent Number</b>     | Patent pending   |
| <b>Pipe, quantity</b>    | 0  |
| <b>Sectors, quantity</b> | 1  |
| <b>Tower Taper</b>       | Non-tapered   Tapered  |

## Dimensions

|                                   |                      |
|-----------------------------------|----------------------|
| <b>Face Width</b>                 | 3.353 m   11 ft      |
| <b>Width</b>                      | 3,352.8 mm   132 in  |
| <b>Face Support Pipe Diameter</b> | 73.025 mm   2.875 in |
| <b>Mounting Diameter, maximum</b> | 218.44 mm   8.6 in   |
| <b>Mounting Diameter, minimum</b> | 38.1 mm   1.5 in     |
| <b>Pipe Outer Diameter</b>        | 73.025 mm   2.875 in |
| <b>Stand-off Distance</b>         | 1,066.8 mm   42 in   |

## Material Specifications

# SFG22RHDX-11-B

---

**Material Type** Hot dip galvanized steel

## Mechanical Specifications

**Wind Rating** For Specifications, please contact [steelproducts@commscope.com](mailto:steelproducts@commscope.com) or call 800-255-1479

## Packaging and Weights

**Included** Frame | Stiff arms (2) | Tower attachment

**Packaging quantity** 1

## Regulatory Compliance/Certifications

| Agency     | Classification                    |
|------------|-----------------------------------|
| CHINA-ROHS | Above maximum concentration value |
| ROHS       | Compliant/Exempted                |
| UK-ROHS    | Compliant/Exempted                |



## \* Footnotes

**Wind Rating** BWS—Base Wind Speed; FBC—Florida Building Code