

UDGSPSPK2

Base Product

Ultra Low Loss (ULL) Singlemode, SN/APC to SN/APC, 2-Fiber, Ruggedized Fanout Cable Plenum

Product Classification

Regional Availability	Asia Australia/New Zealand China EMEA Europe India Latin America North America
Portfolio	CommScope®
Product Type	Ruggedized fanout
Product Brand	SYSTIMAX ULL
Product Series	UDG
Ordering Note	For additional jacket colors, please contact a CommScope Sales Representative For lengths greater than 999 ft (304 m), orders must be in meters Minimum length may vary based on cable configuration

General Specifications

Color, boot A	Green
Color, connector A	Green
Color, boot B	Green
Color, connector B	Green
Construction Type	Stranded
Interface, Connector A	SN/APC
Interface, Connector B	SN/APC
Jacket Color	Yellow
Polarity	Method B Enhanced
Total Fibers, quantity	2

Mechanical Specifications

Cable Retention Strength, maximum	11.24 lb @ 0 ° 4.40 lb @ 90 °
--	---------------------------------

Optical Specifications

Fiber Mode	Singlemode
Fiber Type	G.657.A2, TeraSPEED®

Environmental Specifications

UDGSPSPK2

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Environmental Space	Plenum

Included Products

760251282 P-002-DU-8G1-M15YL/AY/LTS	-	Fiber indoor cable, LazrSPEED® Plenum Light Duty Interconnect Cordage, 2 fiber, G.657.A2, Meters jacket marking, Yellow jacket color
--	---	--