

# 760258662 | FMS-K1BI-L1A1-12-SP-EU



FMS Fiber Optic Panel, 1U, 19 in, black, Includes 6 x LC SM Duplex Adaptors (12F), 12 x SM LC Pigtails. 12 x Splice protectors. Splice tray and cable glands

## Product Classification

<b>Regional Availability</b>	EMEA
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber patch/splice panel
<b>Product Series</b>	FMS

## General Specifications

<b>Functionality</b>	Patching   Splicing
<b>Body Style</b>	Symmetrical
<b>Cable Exit Location</b>	Rear, left side
<b>Color</b>	Black
<b>Interface, front</b>	LC/UPC
<b>Fiber Color Code</b>	TIA-598
<b>Rack Type</b>	EIA 19 in
<b>Rack Units</b>	1
<b>Shelf Movement</b>	Sliding
<b>Splice Trays Included, quantity</b>	1
<b>Splicing Type</b>	Heat shrink, single fiber fusion
<b>Total Ports, quantity</b>	12

## Dimensions

<b>Height</b>	44.3 mm   1.744 in
<b>Width</b>	482.2 mm   18.984 in
<b>Depth</b>	344.2 mm   13.551 in

## Material Specifications

<b>Finish</b>	Powder coated
---------------	---------------

**Material Type** Steel

## Optical Specifications

**Fiber Mode** Singlemode

**Fiber Type** G.657.A1

**Insertion Loss, maximum** 0.3 dB

**Return Loss, minimum** 45 dB

## Packaging and Weights

**Included** Mounting hardware

**Packaging quantity** 1

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

