

1 2 3 4 5 6 7 8 9 10 11 12

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED

A

B

C


D

E

F

G

H



NHH-55C-HG-R2B

**COMMSCOPE, INC. OF NORTH CAROLINA**

TOLERANCES		SAP MATERIAL MASTER	
0 PLACE	X ±	2 PLACE	.XX ±
1 PLACE	.X ±	ANGLES	±
FINISH		MATERIAL	
<small>UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS INTERPRET PER ISO STANDARDS HANDBOOK TECHNICAL DRAWINGS VOLUMES 1 &amp; 2, THIRD EDITION (2002)</small>	NAME	DATE	TITLE
	CE NPHATAK	03/14/2023	<b>PRODUCT DRAWING</b>
	RW NPHATAK	04/11/2023	
	AD MB1140	04/12/2023	SCALE: <b>1:8</b>
	RE RK1070	04/12/2023	
ECN 40167210CMO			DOCUMENT NO. <b>NHH-55C-HG-R2B</b>
DENSITY	g/mm <sup>3</sup>	SIZE	WORK AREA
MASS	grams	A2	BSA
VOLUME	mm <sup>3</sup>	MODEL	
SURFACE AREA	mm <sup>2</sup>	VERSION	STATUS
HEIGHT		00	RE
LENGTH		DRAWING	
WIDTH		REVISION	VERSION
		A	00
		STATUS	REVISION
		RE	A
		SHEET	
		1 OF 1	

1 2 3 4 5 6 7 8 9 10 11 12